





linear dimension(Tolerances Standard GB/T 14486-2008)								—   		
variable range	to 6	over 6 to 10	over 10 to 30	over 30 to 60	over 60 to 100	over 100 to 160	over 160 to	to 10	over 10 to 100	over 100 to
tolerance	±0.20	±0.30	±0.50	±0.70	±1.00	±1.30	±1.60	0.10	0.30	0.60



REVISION RECORD				
REV.	DESCRIPTION	ECN No.	APPROVED	DATE
A	新发行		CLF	21.03.15

UL/CUL 技术 参数 UL/CUL Technical Data					
等 级	Use Group		B	C	D
额定电压	Rated Voltage	[V]	300	-	300
额定电流	Rated Current	[A]	8	-	10
接线范围	Wire Range		-		
单/多芯线	Solid/Stranded	[AWG]			
耐电压	Withstanding Voltage		1600V/1Min		
IEC 技术参数 IEC Technical Data					
过电压类别	Overvoltage Category		III	III	II
污染等级	Contamination Class		-	2	2
额定电压	Rated Voltage	[V]	-	160	320
额定电流	Rated Current	[A]	-	7	7
额定冲击电压	Impulse withstand voltagea	[KV]	-	2.5	2.5
导线截面积	Conductor cross section		-		
硬质/柔性导线	Solid/ flexible	[mm²]			
材 料			Material		
绝缘材料	Insulation Material		PA66		
阻燃等级	Imflammability		UL94V-0		
导体材料	Contactur Material		铜合金 Copper alloy		
导体表面镀层	Contactive Coating		镀锡 Tin Plated		
一般参数			Other Data		
间距	Pitch	[mm]	3.5		
极数	Poles	[P]	2-24		
剥线长度	Stripping Length	[mm]	-		
螺丝	Screw/ 扭矩	Torque(Max)	[N.m]		
工作温度	Operating temperatur	[°C]	-40~+105		
引针尺寸	Pin Dimensions	[mm]	3.7		
PCB板孔径	PCB Hole Diameter	[mm]	1.4		

DES.	FZM	DATE	21.03.15
CHK.	SY	DATE	21.03.15
APP.	CLF	DATE	21.03.15

单位 / UNITS	mm	尺寸 / SIZE	A4	比例 / SCALE	1:1	第三视角 / THIRD ANGLE PROJECTION	版本 / REV	A
						名称 / TITLE	KF2EDGRM-3.5	



慈溪市科发电子有限公司
CIXI KEFA ELECTRONIC CO., LTD