







REV	DESCRIPTION	DESIGN	APPROVAL	DATE
A0	NEW VERSION	Colinye	Jerry	




NOTES:

1. Material/材质:
Retainer/二次锁: PA66 UL94 V-0 Low halogen/无卤; Color/颜色:Natural/本色;
2. The surface of the product shall be free of excessive plastic, lack of plastic, mottle, etc
产品表面不能有多胶、缺胶、杂色等现象;
3. Bow 0.38mm MAX. per 25.4mm on surface C /C平面上每25.4mm最大弯曲0.38mm
3. RoHS Compliance/产品符合RoHS
4. Applicable Housing/适配塑胶主体961-XX12-117;
5. Order Information/编码原则: 968-XX17-117

See table/参

Poles	P/N	DIM "A"	DIM "B"
4	968-0417-117	9.70	7.05
6	968-0617-117	12.70	10.05
8	968-0817-117	15.70	13.05
10	968-1017-117	18.70	16.05
12	968-1217-117	21.70	19.05
14	968-1417-117	24.70	22.05
16	968-1617-117	27.70	25.05
18	968-1817-117	30.70	28.05
20	968-2017-117	33.70	31.05
22	968-2217-117	36.70	34.05
24	968-2417-117	39.70	37.05

X± 0.50	X'± 1°
.X± 0.35	.X'± 0.5°
.XX± 0.25	.XX'± /
.XXX± 0.15	.XXX'± /
UNITS:	mm
The information in this document is property of JiDC company and should not be copied or reproduced in any other way, without written permission.	

 Guangdong JiDe Precision Electronics Co., Ltd 广东济德精密电子有限公司	
TITLE: 3.0mm PITCH RETAINER	PART NO. 968-XX17-117
APPD:	DWG NO: C-968-XX17-117
CHKD:	
DRAW:	
	SCALE 2.5:1
	SHEET 1/1
	REV. A0