



SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance:20mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40℃ to +105℃


Contact Material:Copper Alloy

Contact Plating:Au or Sn Over Ni


Insulator Material:Polyester(UL94V-0)

Standard: PBT

Max.Processing Temp: 230℃±5℃ 5S





Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

2285	02	XX	X	N	XX	R	Y	X	XX
No.of Pins Per Row 02~40P	Insulator Option A=BK-PBT C=BK-PA6T E=BK-PA9T F=BK-LCP	Material	Contact Plating G1:Gold Flash G2:1.5u" Gold G3:2u" Gold G4:3u" Gold G5:5u" Gold G6:10u" Gold G7:15u" Gold G8:30u" Gold S0:Gold Flash/Tin SN:Tin	Packing 0=PE Bag A=Tray T=Tube P=Tube+Cap R=Reel+Cap M=Reel+Mylar	code stream 01~99				



				OPERATION		DRAW	YiYuSheng	20.03.28	SCALE	FIT	JILN ® 深圳市锦凌电子有限公司 SHENZHEN JINLING ELECTRONICS CO.,LTD Tel: 86-755-27483253 Fax: 86-755-2997-5588	
				X.X	±0.30				UNIT	mm		
A	A0	2020.03.28	NEW DRAWING	X.XX	±0.20	CHECK			SIZE	A4	PART NO.	228502XXXNXXRYXXX
				X.XXX	±0.10				SHEET	1/1		
				Angle	±3°	APPROVE			PROJ.	1/1	TITLE:	2.54PF H8.5mm 2xNpin 90°
	REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM							