



TE Internal #: 1775060-1
B, 2.0, Mini Profile, Receptacle, 1 Port, Top, Vertical, Tray, Flush,
Through Hole - Solder, Cable-to-Board, 5000, 5 Position, USB
Connectors
[View on TE.com >](#)

Connectors > Audio & Video Connectors > USB Connectors



USB Adapter Type: **B**
USB Version: **2.0**
Connector Profile: **Mini**
Connector & Housing Type: **Receptacle**
Number of Ports: **1**

Features

Product Type Features

Integral Locking Latch	Without
USB Adapter Type	B
USB Version	2.0
Connector & Housing Type	Receptacle
Connector System	Cable-to-Board
Connector & Contact Terminates To	Printed Circuit Board
USB Connector Type	Mini USB 2.0 Type-B

Configuration Features

Number of Ports	1
Number of Positions	5

Body Features

Offset	0 mm
Shell Plating Finish	Bright
Shell Plating Material	Tin over Copper
Connector Profile	Mini

Contact Features

Contact Mating Area Plating Material Thickness	.76 µm[29.92 µin]
Contact Mating Area Plating Material	Gold Flash over Palladium Nickel



Contact Current Rating (Max)	1 A
------------------------------	-----

Termination Features

Termination Post & Tail Length	1.2 mm[.047 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Locking Feature	With
PCB Mount Location	Top
PCB Connector Seating	Flush
PCB Mount Retention Type	Straight Leg
Connector Mounting Type	Board Mount

Housing Features

Housing Material	PBT
Housing Color	Black
Body Orientation	Vertical
Centerline (Pitch)	.8 mm[.031 in]

Dimensions

PCB Thickness (Recommended)	.8 mm[.032 in]
-----------------------------	----------------

Usage Conditions

Soldering Temperature (Max)	240 °C[464 °F]
Mating Cycles (Max)	5000
Operating Temperature Range	-20 – 60 °C[-4 – 140 °F]

Operation/Application

Halogen Free	No
Circuit Application	Power & Signal

Industry Standards

Moisture Sensitivity Level	1
Industry Standard	USB 2.0
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	150
Packaging Method	Tray



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1734205-1
MINI USB, TYPE B, PLUG. CABLE-KIT

TE Part # 1496476-1
STD USB-A TO MINI-B ASSY, 1M

TE Part # 1929690-1
USB CABLE, USB A to Mini USB,Blue

Customers Also Bought



TE Part #2110304-1
SFP+ 1x1 Cage Assembly, Solder Tail

TE Part #1734366-3
Std USB Type A, VT, T/H, Blue

TE Part #2023246-2
ASS'Y SATA REC. R/A SMT TYPE 3.45H

TE Part #2174507-2
MICRO USB, TYPE B

TE Part #1-1734035-2
MINI USB, TYPE B, R/A, SMT

TE Part #6450863-5
MBXLE VERT RCPT 7ACP

TE Part #5177984-6
0.8FH,P05H.5,140,08/Sn,TU

TE Part #1747981-2
Std HDMI, RA, SMT

TE Part #2007435-3
Std HDMI, Flag, T/H

Documents

Product Drawings

MINI USB, TYPE B, VERTICAL, T/H

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1775060-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1775060-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1775060-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



MINI USB SERIES CONNECTOR

English

Product Specification

English