




RoHs

VER	MARK	PR. BY	DESCRIPTION	DATE

PIN number variable size comparison table					
PART NO	Pin	A	B	C	D
W200113K-2PW2431	2	2.00	8.00	2.50	4.90
W200113K-3PW2431	3	4.00	10.00	2.50	6.90
W200113K-4PW2431	4	6.00	12.00	5.00	8.90
W200113K-5PW2431	5	8.00	14.00	7.00	10.90
W200113K-6PW2431	6	10.00	16.00	9.00	12.90
W200113K-7PW2431	7	12.00	18.00	11.00	14.90
.....					
W200113K-16PW2431	16	30.00	36.00	29.00	32.90

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 2.0
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 2A AC DC
- 4.Insulation Resistance: 800MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X.X ±0.30	X.° ±5°	PART NO. W200113K-XPW2431	TITLE: WAFER 2.00 立贴带扣		
.XX ±0.20	X.X° ±1°				
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER	SIZE A4	UNITS MM
MANUFACTURE DWG		CHED: Talen		SCALE	SHEET
		APPD: Sophia		N:A	1/1