

A	Dept					5	6	7	8	A		
	Qty	晨翔2.54mm Wafer 2510 Type, 7Pin母头胶芯, 象牙白				REV.	DESCRIPTION	DRAWN	CHECKED		APPROVED	
	DC	1					A	NEW RELEASE	WPY 11/08/24'			
	ED	1										
	IE	1	晨翔料号: I-DS1070-SCV07									
B	ISO	1										
	PD	1										
	R&D	1										
	SD	1										
	QA	1										
C	QC	1										
	QF	1										
D												
E												
F												
G												
H												

晨翔2.54mm Wafer 2510 Type, 7Pin母头胶芯, 象牙白

晨翔料号: I-DS1070-SCV07

REV. A DESCRIPTION NEW RELEASE DRAWN WPY 11/08/24' CHECKED  APPROVED

1. 电性说明:
1.1 接触阻抗: 30毫欧最大
1.2 耐压: 600伏交流电一分钟
1.3 绝缘阻抗: 1000兆欧最小
1.4 额定电流: 3安
2. 环境特性:
2.1 工作温度: -25~+85° C
3. 材料:
3.1 胶芯: 尼龙, 象牙白

18.44
15.24
2.54
4.9
6.0
7.5
13.2

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	2.54mm Wafer 2510 Type, 7Pin母头胶芯, 象牙白	
X.	±0.60	X.	±5°	UNITS	mm			
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES	DS1070 SERIES	
.XX	±0.25	.XX	±2°	 晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD				
DRAWING TYPE		CUSTOMER						
SCALE		1:1	SHEET 1 OF 1					
DRAWING NO.		C-DS1070-XXXXX-A						