




RoHs


技术要求 Specification:


- 1、材质 Material: PA66 UL94V-0:
- 2、额定电流 Current rating:3.0A AC,DC
- 3、额定电压 Voltage rating:250V AC,DC
- 4、温度范围 Temperature range:-25℃ to+85℃
- 5、接触电阻 Contact resistance:≤20mΩ
- 6、绝缘电阻 Insulation resistance:≥1000MΩ
- 7、耐压 Withstand voltage:1000V AC/minute
- 8、塑件表面平整光洁，无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious glitches, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

VER	MARK	PR. BY	DESCRIPTION	DATE

PIN number variable size comparison table			
PART NO	PIN	A	B
W25411K-2PW113	2	2.50	5.80
W25411K-3PW113	3	5.00	8.30
W25411K-4PW113	4	7.50	10.80
W25411K-5PW113	5	10.00	13.30
W25411K-6PW113	6	12.50	15.80
W25411K-7PW113	7	15.00	18.30
W25411K-8PW113	8	17.50	20.80
.....			
W25411K-17PW113	17	40.00	43.30



GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd	
X.X ±0.30	X.° ±5°	PART NO.	TITLE:
.XX ±0.20	X.X° ±1°	W25411K-XPW113	HA2.5MM HOUSING
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER
MANUFACTURE DWG		CHED: Talen	SIZE A4
		APPD: Sophia	UNITS MM
			SCALE N:A
			SHEET 1/1