





品 名	X. X
RT-C14B-D1+RT-S01-2BR	0.8mm
RT-C14B-D2+RT-S01-2BR	1.0mm
RT-C14B-D3+RT-S01-2BR	1.5mm
RT-C14B-D4+RT-S01-2BR	2.0mm
RT-C14B-D5+RT-S01-2BR	3.0mm
RT-C14B-D6+RT-S01-2BR	1.2mm

Socket : RT-C14B-D**-13-R

1.Rating : 10A 250VAC (CCC ; UL ; CUL)

2.Insulation resistance : >100MΩ Min 500VDC

3.Withstand voltage : >2000VAC 0.5mA 1 minute

Switch : RT-S01-113-L4LBR 带红色灯

1.Rating : 10A 125VAC 6A 250VAC (UL ; CUL ; CQC)

10(4)A 250V~ (VDE)

2.Contact resistance : <50mΩ

3.Insulation resistance : >100MΩ Min 500VDC

4.Dielectric strength : >1500VAC 0.5mA 1 minute

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE				LMC	SCALE	NO		
3	→	8	→	X	±0.30				2019.05.20	MAT'L	***		
2	→	7	→	X.X	±0.20					MATERIAL NO.			
1	→	6	→	X.XX	±0.10	LEGION ELECTRONIC & HARDWARE CO., LTD.				DRAWING NO.		REV.	
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°					RT-C14B-D3+RT-S01-2BR		*****	