




VER	MARK	PR. BY	DESCRIPTION	DATE

PIN number variable size comparison table			
PART NO	PIN	A	B
W2542110-2PW2113	2	2.50	7.50
W2542110-3PW2113	3	5.00	10.00
W2542110-4PW2113	4	7.50	12.50
W2542110-5PW2113	5	10.00	15.00
W2542110-6PW2113	6	12.50	17.50
.....			
W2542110-20PW2113	20	47.50	52.50

2	端子 Contact	黄铜	N*1	电镀(锡):整个表面 镀底镍 30u"MIN, 再镀锡 80u"MIN
1	基座 Wafer	PA66 (UL94V-0)	1	白色
序号	名称	材料	数量	备注

GENERAL TOLERANCES UNLESS SPECIFIED		PART NO.		TITLE:	
X.X	±0.30	X.*	±5°	W2542110-XPW2113	XH2.54MM 直针
.XX	±0.20	X.X*	±1°	DESIGN: James	CUSTOMER
.XXX	±0.10	X.XX*	±0.5°	CHED: Talen	SIZE A4
MANUFACTURE DWG		APPD: Sophia	SCALE N:A		UNITS MM
			SHEET 1/1		

- 技术要求:
1. 塑件材料 :PA66 (UL-94V-0)
 2. 接触件 :黄铜镀锡
 3. 接触电阻 :≤10mΩ
 4. 绝缘电阻 :≥100MΩ
 5. 额定电压 :250V AC DC
 6. 额定电流 :2.0A AC DC
 7. 耐压 :能承受 1000V AC/Minute
 8. 工作温度 :-25° ~+85°
 9. 可焊性试验 :浸锡面积 ≥95% 温度 235±5°, 时间 2.5±0.5 秒
 10. 铅和镉等六大有害物质含量要符合环保要求.