

12345678

Dept
Qty

晨翔2.54mm Wafer 2510 Type, 8Pin母头胶芯, 象牙白

晨翔料号: I-DS1070-SCV08

REV. DESCRIPTION DRAWN CHECKED APPROVED

A NEW RELEASE WPY 11/08/24'

DC 1

ED 1

FE 1

ISO 1

PD 1

R&D 1

SD 1

QA 1

QC 1

QE 1

1. 电性说明:

1.1 接触阻抗: 30毫欧最大

1.2 耐压: 600伏交流电一分钟

1.3 绝缘阻抗: 1000兆欧最小

1.4 额定电流: 3安

2. 环境特性:

2.1 工作温度: -25~+85° C

3. 材料:

3.1 胶芯: 尼龙, 象牙白

20.98

17.78

2.54

4.9

6.0

7.5

13.2

GENERAL TOLERANCE

ANGLE TOLERANCE

PROJECTION

TITLE

2.54mm Wafer 2510 Type, 8Pin母头胶芯, 象牙白

UNITS mm

SHEET SIZE A4

SERIES DS1070 SERIES

DRAWING TYPE CUSTOMER

SCALE 1:1 SHEET 1 OF 1

DRAWING NO. C-DS1070-XXXXX-A

晨翔电子有限公司

CONNFLY CONNFLY ELECTRONIC CO. LTD

12345678