




RoHS

技术要求 Specification:

- 1、材质 Material: PA66 UL94V-0:
- 2、额定电流 Current rating:1.0A AC,DC
- 3、额定电压 Voltage rating: 50V AC,DC
- 4、温度范围 Temperature range:-25℃ to+85℃
- 5、接触电阻 Contact resistance:<30mΩ
- 6、绝缘电阻 Insulation resistance:>100MΩ
- 7、耐压 Withstand voltage:500V AC/minute
- 8、塑件表面平整光洁，无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrsbubbles, distortion, gate strain, lack of material and otherundesirable phenomena.

PIN number variable size comparison table

Part No	Pin	A	B	C	D
W12511K-2PY113	2	1.25	2.00	3.75	
W12511K-3PY113	3	2.50	3.20	5.00	
W12511K-4PY113	4	3.75	4.30	6.25	
W12511K-5PY113	5	5.00	4.30	7.50	6.25
W12511K-6PY113	6	6.25	6.25	8.75	8.75
W12511K-7PY113	7	7.50	6.25	10.00	8.75
W12511K-8PY113	8	8.75	6.25	11.25	8.75
W12511K-9PY113	9	10.00	6.25	12.50	8.75
W12511K-10PY113	10	11.25	8.30	13.75	10.70
W12511K-11PY113	11	12.50	8.30	15.00	10.70
W12511K-12PY113	12	13.75	8.30	16.25	10.70
W12511K-13PY113	13	15.00	8.30	17.50	10.70
W12511K-14PY113	14	16.25	8.30	18.75	10.70
W12511K-15PY113	15	17.50	8.30	20.00	10.70
W12511K-16PY113	16	18.75	8.30	21.25	

GENERAL TOLERANCES
UNLESS SPECIFIED

X.X ±0.30 X.° ±5°

.XX ±0.20 X.X° ±1°

.XXX ±0.10 X.XX° ±0.5°

MANUFACTURE DWG



深圳市华明通电子有限公司

Shenzhen Huamingtong Electronics Co., Ltd

PART NO.

W12511K-XPY113

DESIGN: James

CHED: Talen

APPD: Sophia

TITLE:

GH1.25MM HOUSING

CUSTOMER

SCALE

N:A

SIZE

A4

SHEET

1/1

UNITS

MM

SHEET

1/1