

RoHs





VER	MARK	PR. BY	DESCRIPTION	DATE

技术要求:



- 1、塑件材料: LCP (UL-94V-0)
- 2、接触件: 黄铜镀锡
- 3、接触电阻: $\leq 30\text{m}\Omega$
- 4、绝缘电阻: $\geq 1000\text{M}\Omega$
- 5、额定电压: 250V AC DC
- 6、额定电流: 3.0A AC DC
- 7、耐压: 能承受 1000V AC/Minute
- 8、工作温度: $-25^{\circ}\sim+85^{\circ}$
- 9、可焊性试验: 浸锡面积 $\geq 95\%$ 温度 $250^{+0.5}_{-0}$. 时间 2.5 ± 0.5 秒.
- 10、铅和镉等六大有害物质含量要符合环保要求

PIN number variable size comparison table

PART NO	PIN	A	B	C
W200121K-6PY2413	6	4.00	8.00	6.90
W200121K-8PY2413	8	6.00	10.00	8.90
W200121K-10PY2413	10	8.00	12.00	10.90
W200121K-12PY2413	12	10.00	14.00	12.90
W200121K-14PY2413	14	12.00	16.00	14.90
.....				
W200121K-30PY2413	30	28.00	32.00	30.90



SUGGESTED PCB LAYOUT
(COMPONENT SIDE)



SECTION A-A

GENERAL TOLERANCES
UNLESS SPECIFIED

X.X	± 0.30	X. $^{\circ}$	$\pm 5^{\circ}$
.XX	± 0.20	X.X $^{\circ}$	$\pm 1^{\circ}$
.XXX	± 0.10	X.XX $^{\circ}$	$\pm 0.5^{\circ}$

MANUFACTURE DWG




深圳市华明通电子有限公司

Shenzhen Huamingtong Electronics Co., Ltd

PART NO.
W200121K-XPY2413

TITLE:
PHB2.0 双排直针带扣

DESIGN: James
CHED: Talen
APPD: Sophia



SIZE	UNITS
A4	MM
SCALE	SHEET
N:A	1/1