



A	—
B	—
C	—
D	—
E	—
F	—
G	—
H	—

					REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED	A
晨翔2.54mm Wafer 2510 Type, 3pin 公头, 弯插, 象牙白, 全锡, TYPE A					A	NEW RELEASE	WPY 11/08/24'			
晨翔料号: DS1070-3MRV6A										



PCB板孔尺寸参考
公差: ± 0.05

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	2.54mm Wafer 2510 Type, 3pin 公头, 弯插, 象牙白, 全锡, TYPE A	
X.	±0.60	X.	±5°	UNITS	mm			
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES	DS1070 SERIES	
.XX	±0.25	.XX	±2°	 晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD				
DRAWING TYPE		CUSTOMER						
SCALE	1:1	SHEET	1 OF 1					
DRAWING NO.	C-DS1070-XXXXX-A							

备注:

1. 电性说明:

1.1 接触阻抗：30毫欧最大

1.2 耐压：600伏交流电一分钟

1.3 绝缘阻抗：1000兆欧最小

1.4 额定电流：3安

2. 环境特性:

2.1 工作温度: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$

3. 材料:

3.1 端子：磷铜，镀锡

3.2 胶芯：尼龙,象牙白,阻燃

4. 产品符合欧盟RoHS环保要求