






Technical Index:

1. Temperature range: -25°C~85°C.
2. Rated voltage: 250V DC/AC(rms).
3. Rated current: 5A AC, DC.
4. Contact resistance: ≤20mΩ.
5. Dielectric withstanding voltage): 1500V AC/minute.
6. Insulation resistance: ≥1000MΩ.
7. Apply to gauge): AWG#20~#24.

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd	
X.X ±0.30	X.° ±5°	PART NO. W3002-DZ221	TITLE: MX3.0MM TERMINAL
.XX ±0.20	X.X° ±1°		
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER
MANUFACTURE DWG		CHED: Talen	
		APPD: Sophia	
			SIZE A4
			UNITS MM
			SCALE N:A
			SHEET 1/1