




技术指标 :

- 1. 温度范围 : $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
- 2. 额定电压 :150V AC, DC.
- 3. 耐电压 :500V AC/minute.
- 4. 接触电阻 : $\leq 20\text{m}\Omega$ (Initial)
 $\leq 40\text{m}\Omega$ Change allowed.
- 5. 绝缘电阻 : $\geq 500\text{M}\Omega$.
- 6. 额定电流 :1A AC, DC.

VER	MARK	PR. BY	DESCRIPTION	DATE

PIN number variable size comparison table				
PART NO	PIN	A	B	C
W125120-10PY123	2*5	10.50	5.00	7.86
W125120-12PY123	2*6	11.75	6.25	9.11
W125120-14PY123	2*7	13.00	7.50	10.36
W125120-16PY123	2*8	14.25	8.75	11.61
W125120-18PY123	2*9	15.50	10.00	12.86
W125120-20PY123	2*10	16.75	11.25	14.11
W125120-22PY123	2*11	18.00	12.50	15.36
W125120-24PY123	2*12	19.25	13.75	16.61
W125120-28PY123	2*14	21.75	16.25	19.11
W125120-30PY123	2*15	23.00	17.50	20.36
W125120-32PY123	2*16	24.25	18.75	21.61
W125120-34PY123	2*17	25.50	20.00	22.86
W125120-36PY123	2*18	26.75	21.25	24.11
W125120-38PY123	2*19	28.00	22.50	25.36
W125120-40PY123	2*20	29.25	23.75	26.61
.....	...			
W125120-50PY123	2*25	35.50	30.00	32.86

GENERAL TOLERANCES UNLESS SPECIFIED		HMTconn 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd		
X.X ±0.30	X.° ±5°	PART NO. W125120-XPY123	TITLE: 1.25 Pitch A型(DF13)双排公头胶壳	
.XX ±0.20	X.X° ±1°			
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER	SIZE
MANUFACTURE DWG		CHED: Talen		UNITS
		APPD: Sophia		MM
			SCALE	SHEET
			N:A	1/1