






HSF RoHS




SPECIFICATIONS

Rated Current:3AMP
Contact Resistance:50mΩ Max
Withstand Voltage:1000VAC for 1 minute
Insulation Resistance:1000MΩ Min
Operation Temperature:-20℃ to +85℃
Mating force:1.96N Max
Un-mating force:0.49N Min



Contact Material:Copper Alloy
Contact Plating:Au Over Ni
Housing Materials: PBT UL94V-0



Mating Draw (Ref)



A-A SECTION



P.C.B Layout

				OPERATION		DRAW	zhouqiyong	2023. 03. 02	SCALE	FIT	JILN® 深圳市锦凌电子有限公司 SHENZHEN JINLING ELECTRONIC CO.,LTD Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992	
				X. X	±0. 30				UNIT	mm		
				X. XX	±0. 20	CHECK			SIZE	A4		
				X. XXX	±0. 10				SHEET	1/1		
A0	2023. 03. 02	NEW DRAWING		Angle	±3°	APPROVE			PROJ.		TITLE:	四排四芯母座黑色 第二代
REV	DATE	MODIFICATION DESCRIPTION		DIM	TOL							
1	2	3	4	5	6	7	8	9				