







SCHEMATIC



P.C.B LAYOUT



H	L
4.3	3.15
5.0	3.85
6.0	4.85
7.0	5.85
7.3	6.15
7.5	6.35
8.0	6.85
8.5	7.35
9.0	7.85
9.5	8.35
10.0	8.85
11.0	9.85
12.0	10.85
13.0	11.85
14.0	12.85
15.0	13.85
15.5	14.35
16.0	14.85
17.0	15.85

					TOLERANCE					
					UNLESS SPECIFIED					
					UP TO 5mm: ±0.1	ANGULAR				
					ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS	BY APPD
5	SHRAPNEL	SUS	1	Ag-Plated	TITLE: TACT SWITCH		UNIT : MM	ROHS	DWN	
4	COVER	SPCC	1	Ni-Plated	MODEL: TC-00100GD-050C		SCALE: 1:1	COMPLIANT	CHK'D	
3	TERMINA	BRASS	1	Ag-Plated	东莞市六钧电子五金有限公司				APPD	
2	KNOB	PPA/PA66	1	BLACK						
1	CASE	PPA/PA66	1	BLACK/Ag-Plated						
NO.	PART NAME	MATERIAL	QTY	FINISHING					PRO.AGL:	REV :A0