





SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40℃ to +105℃

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Soldering temperature:260℃±5° 5S





Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

1225 13 XX X N XX R XXX X XX

No.of Pins
01~40P
Insulator
Option
Material
A=BK-PBT
C=BK-PA6T
E=BK-PA9T
F=BK-LCP
Contact Plating
G0:Gold Flash
G1:1u" Gold
G2:1.5u" Gold
G3:2u" Gold
G4:3u" Gold
G5:5u" Gold
G6:10u" Gold
G7:15u" Gold
G8:30u" Gold
S0:Gold Flash/Tin
SN:Tin
Pin Length
Packing
0=PE Bag
A=Tray
T=Tube
code stream
01~99



Dimension antitheses list

ITEM	PA	PB	PC
Standard	6.00	9.54	3.00

OPERATION

X.X ±0.30
X.XX ±0.20
X.XXX ±0.10
Angle ±3°
DIM TOL

DRAW

CHECK

APPROVE

YiYuSheng

12.04.18

SCALE

FIT

UNIT

SIZE

SHEET

PROJ.

mm

A4

1/1

PROJ.

JILN® 深圳锦凌电子股份有限公司
SHENZHEN JINLING ELECTRONICS CO.,LTD

Tel: 86-755-27483253 Fax: 86-755-2997-5588

PART NO.

122513XXXNXXRXXXXXX

TITLE:

2.54PH H2.5mm 3xNpin 90°

1

2

3

4

5

6

7

8

9