

HSF

SPECIFICATIONS

Rated Current:3AMP

Contact Resistance:50mΩ Max

Withstand Voltage:1000VAC for 1 minute

Insulation Resistance:1000MΩ Min

Operation Temperature:-20°C to +85°C





Mating force:1.96N Max

Un-mating force:0.49N Min


Contact Material:Copper Alloy

Contact Plating:Au Over Ni



Housing Materials: PBT UL94V-0



A-A SECTION



Mating Draw (Ref)



P.C.B Layout

OPERATION

X.X ±0.30

X.XX ±0.20

X.XXX ±0.10

Angle ±3°

DIM TOL

DRAW

OUYANG

21.12.11

SCALE

FIT

UNIT

mm

SIZE

A4

SHEET

1/1

PROJ.

PROJ.

JILN® 深圳市锦凌电子有限公司
SHENZHEN JINLING ELECTRONICS CO.,LTD
Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992

PART NO.

8310-F03G1AB01

TITLE:

四排三芯母座黑色

A

A0

2021.12.11

NEW

DRAWING

MODIFICATION

DESCRIPTION

CHANGE

APPROVE

1

2

3

4

5

6

7

8

9

A