

HSF**SPECIFICATIONS**

Rated Current:3AMP

Contact Resistance:50mΩ Max

Withstand Voltage:1000VAC for 1 minute

Insulation Resistance:1000MΩ Min

Operation Temperature:-20°C to +85°C

Mating force:1.96N Max

Un-mating force:0.49N Min






Contact Material:Copper Alloy

Contact Plating:Au Over Ni


Housing Materials: PBT UL94V-0

Bottom Cover Materials: PC UL94V-0


Top Cover Materials: PC UL94V-0



A-A SECTION



打开状态



压合状态



B-B SECTION

主体颜色	上压盖颜色	上压盖线径	主体线径
黑色	紫色	Φ 0.6-0.8	AWG26-24 0.13-0.21MM ²
	红色	Φ 0.8-1.0	
	黄色	Φ 1.0-1.2	
	橙色	Φ 1.2-1.6	
	绿色	Φ 1.0-1.2	
	蓝色	Φ 1.2-1.6	
	灰色	Φ 1.6-2.0	AWG20-22 0.32-0.50MM ²

JILIN® 深圳市锦凌电子有限公司
SHENZHEN JINLING ELECTRONICS CO.,LTD

Tel: 86-755-27483253 Fax: 86-755-2997-5992

PART NO. 8310-M04G1AX0X

TITLE: 四芯公座

				OPERATION	DRAW	OUYANG	22.03.02	SCALE	FIT
				X.X	± 0.30			UNIT	mm
				X.XX	± 0.20	CHECK		SIZE	A4
				X.XXX	± 0.10			SHEET	1/1
A	A0	2022.03.02	NEW DRAWING	Angle	± 3°	APPROVE		PROJ.	
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL				