





Rated Current:1.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40℃ to +105℃

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Soldering temperature:260℃±5° 5S



Ordering Information

1410 12 XX X N XX S XXX X XX

No. of Pins
Per Row
02~50P

Insulator Material
Option
C=BK~PA6T
F=BK~LCP



Contact
G1:1u" Gold
G2:1.5u" Gold
G3:2u" Gold
G4:3u" Gold
G5:5u" Gold
G6:10u" Gold
G7:15u" Gold
G8:30u" Gold
S0:Gold Flash/Tin
SN:Tin

Plating

Pin Length

Packing
A=Tray

code stream
01~99



Dimension antitheses list		
ITEM	PA	PC
Standard	3.90	2.00

				OPERATION		DRAW	YiYuSheng	12.04.18	SCALE	FIT	 深圳锦凌电子股份有限公司 SHENZHEN JINLING ELECTRONICS CO.,LTD Tel: 86-755-27483253 Fax: 86-755-2997-5588	
				X.X	±0.30				CHECK			
				X.XX	±0.20	SIZE	A4	PART NO.				
A0	2012.04.18	NEW DRAWING		X.XXX	±0.10	APPROVE			SHEET	1/1	TITLE:	1.27PH H1.0 2xNpin 180°
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	Angle	±3°				DIM	TOL	PROJ.	