






Technical Specs:

Insulator: Black glass filled polyester PPS
Flammability: UL 94V-0
Sleeve: Brass
Contact clip(6 finger): Beryllium copper(C17200)
Accepted pin: Ø0.70 to 0.90mm,0.635mm
Forces:
--Insertion 2 N typ
--Withdrawal 1 N typ
Mechanical life: min500 cycles
Rated current: 3A
Contact resistance: max 10mΩ
Dielectric resistance: Min 1000V RMS
Coplanarity SMD max 0.1mm(measured on terminations: 25mm long connectors)




Ordering Information

3620 70 1 XX R XX 124 01

No. of Pins
2-40

Contact Plating
G0: Gold Flash
S0: Gold Flash/Tin

Length
124=12.4mm



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE ± 0.05)

OPERATION

X.X ± 0.30

X.XX ± 0.20

X.XXX ± 0.10

Angle ± 3°

DIM TOL

DRAW

CHECK

APPROVE

JinChengXin

19.04.25

SCALE

UNIT

SIZE

SHEET

PROJ.

FIT

mm

A4

1/1

PROJ.

JILN® 深圳市锦凌电子有限公司
SHENZHEN JINLING ELECTRONIC CO.,LTD
Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992

PART NO.

3620701XXRXX12401

TITLE:

2.54X7.0 Machine Socket 90°

A

A