

1 2 3 4 5 6 7 8

Dept

Qty

DC 1

ED 1

IE 1

ISO 1

PD 1

R&D 1

SD 1


QA 1

QC 1

QE 1

晨翔2.54mm排针，2*5PIN, 直插，镀金，黑胶，胶高2.5mm，针长11.6mm

晨翔料号：DS1021-2x5SF11-B

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	JLZ 06/22/24'		

12.70±0.5

5.00

0.64±0.05

2.50

2.54±0.1

10.16±0.25

6.10±0.2

2.54

3.00±0.2

10.16

2.54

ø1.02

2.54

PCB孔位尺寸参考
公差:±0.05

GENERAL TOLERANCE

X. ±0.60

.X ±0.38

.XX ±0.25

ANGLE TOLERANCE

X. ±5°

.X ±3°

.XX ±2°

DRAWING TYPE

CUSTOMER

SCALE

1:1

SHEET

1 OF 1

DRAWING NO.

C-DS1021-XXXXX-A

PROJECTION

UNITS

SHEET SIZE



mm

A4

TITLE

PIN HEADER PITCH 2.54mm V/T TYPE

SERIES

DS1021 SERIES

 晨翔电子有限公司

CONNFLY CONNFLY ELECTRONIC CO. LTD

1 2 3 4 5 6 7 8

备注:

1. 电性说明:

1.1 接触阻抗: 20毫欧最大

1.2 耐压: 600伏交流电一分钟

1.3 绝缘阻抗: 1000兆欧最小

1.4 额定电流: 3安

2. 环境特性:

2.1 工作温度: -40~+105° C

3. 材料:

3.1 端子: H62黄铜, 镍底镀金

3.2 胶芯: PBT, 黑色, 阻燃

4. 焊接条件: 波峰焊250℃, 时间3至5秒

5. 产品符合RoHS环保要求

1 2 3 4 5 6 7 8

1 2 3 4 5 6 7 8