

SPECIFICATIONS

Rated Current:1.0AMP

Contact Resistance:20mΩ Max

Withstand Voltage:500V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:−40℃ to +105℃




Contact Material:Brass

Contact Plating:Au or Sn Over Ni

Insulator Material:Polyester(UL94V−0)

Resistance To Soldering Heat:

260° C±5° C, 10s(PA6T&PA9T&LCP insulator)



Ordering Information

3330 XX M XX X B S X 0X


No. of Pins 6-80 Contact Plating G0:Gold Flash G1:1u" Gold G2:1.5u" Gold G3:2u" Gold G4:3u" Gold G5:5u" Gold G6:10u" Gold G7:15u" Gold G8:30u" Gold 50:Gold Flash/Tin

Insulator Material Option C=BK-PA6T E=BK-PA9T F=BK-LCP

Color Type B=Black

Packing 0=PE Bag A=Troy T=Tube P=Tube+Cap R=Reel+Cap

Serial code



Recommended P.C.B. Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

					OPERATION		DRAW	YTYuSheng	16.01.19	SCALE		FIT	 深圳市锦凌电子有限公司 SHENZHEN JINLING ELECTRONICS CO.,LTD Tel: 86-755-27483253 Fax: 86-755-2997-5588
					X.X	±0.30				UNIT	mm		
					X.XX	±0.20	CHECK			SIZE	A4		
					X.XXX	±0.10				SHEET	1/1		
A0	2016.01.19	NEW DRAWING										TITLE:	1.27DC2-Npin SMT
REV	DATE	MODIFICATION DESCRIPTION			CHANGE	DIM	TOL	APPROVE			PROJ.		
1		2	3	4	5		6	7	8	9			