





SPECIFICATIONS

Rated Current:2.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°c to +105°c

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Soldering temperature:260℃±5° 5S



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

1320 12 XX X X XX M XXX X XX

No.of Pins
Per Row
02~50P



Insulator Material
Option
A=BK-PBT
C=BK-PA6T
E=BK-PA9T
F=BK-LCP

Post
W=With Post
N=W/O Post

Contact Plating
G0:Gold Flash
G1:1u" Gold
G2:1.5u" Gold
G3:2u" Gold
G4:3u" Gold
G5:5u" Gold
G6:10u" Gold
G7:15u" Gold
G8:30u" Gold
S0:Gold Flash/Tin
SN:Tin

Pin Length

Packing code stream
0=PE Bag 01~99
A=Tray
T=Tube
P=Tube+Cap
R=Reel+Cap



Dimension antitheses list

ITEM	PA	PB	W
Standard	3.80	2.50	6.50

JILN® 深圳锦凌电子股份有限公司
SHENZHEN JINLING ELECTRONICS CO.,LTD

Tel: 86-755-27483253 Fax: 86-755-2997-5588

PART NO. 132012XXXXXXMXXXXXX

TITLE: 2.0PH H2.0mm 2xNpin SMT

OPERATION

X.X ±0.30

X.XX ±0.20

X.XXX ±0.10

Angle ±3°

DIM TOL

DRAW

YiYuSheng

12.04.18

SCALE

FIT

UNIT

mm

SIZE

A4

SHEET

1/1

PROJ.

Φ

A0 2012.04.18 NEW DRAWING

REV DATE MODIFICATION DESCRIPTION

CHANGE