

HSF RoHS

NOTES:

Rated Voltage: 250V AC(MAX)

Rated Current: 3A(MAX)

Withstand Voltage: 250V AC RMS for 1Minute

Insulation Impedance: 3000MΩ MIN,at 500V DC

Contact Resistance: 30mΩ(MAX)


Operation Temperature: -45°~+85°

MATERIAL:



Contact: Copper Alloy

Insulation: PBT,UL 94V-0

Shell: SPCC



POS.	DIM A	DIM B	DIM C	DIM D	DIM G
9	30.80	24.99	17.00	19.20	2.77
15	39.20	33.30	25.30	27.60	2.77
25	53.10	47.04	38.96	41.10	2.77
37	69.34	63.50	55.42	57.30	2.77



Ordering Information

6235-02 M XX XX D X X 0X

Connector
Type
F=Female
M=Male

No.of
Pins
09、15、
25、37P

Contact Plating
S0:Gold Flash/Tin
G0:Gold Flash

Color
B=Black
W=White
U=Blue

Packing
T:Tube
A:Tray
O:Pe Bag

				OPERATION		DRAW	OuYangHui	14.03.28	SCALE	FIT	JILN® 深圳市锦凌电子有限公司 SHENZHEN JINLING ELECTRONICS CO.,LTD Tel: 86-755-27483253 Fax: 86-755-2997-5588	
				X.X	± 0.30				UNIT	mm		
				X.XX	± 0.20	CHECK			SIZE	A4		
				X.XXX	± 0.10				SHEET	1/1		
A0	2014.03.28	NEW DRAWING		Angle	± 3°	APPROVE			PROJ.	☯	TITLE:	DB-NP 公 传统焊线式
REV	DATE	MODIFICATION DESCRIPTION		DIM	TOL							