




RoHs

VER	MARK	PR. BY	DESCRIPTION	DATE

SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for 30-60seconds
(260°C for 5seconds)

PIN number variable size comparison table

PART NO	PIN	DIM. A	DIM. B
B25410120-1PB0513-H25A60	1	0.00	2.54
B25410120-2PB0513-H25A60	2	2.54	5.08
B25410120-3PB0513-H25A60	3	5.08	7.62
B25410120-4PB0513-H25A60	4	7.62	10.16
B25410120-5PB0513-H25A60	5	10.16	12.70
B25410120-6PB0513-H25A60	6	12.70	15.24
B25410120-7PB0513-H25A60	7	15.24	17.78
B25410120-8PB0513-H25A60	8	17.78	20.32
B25410120-9PB0513-H25A60	9	20.32	22.86
.....			
B25410120-40PB0513-H25A60	40	(40-1)X2.54	(40)X2.54

GENERAL TOLERANCES
UNLESS SPECIFIED

X.X ±0.30	X.° ±5°
.XX ±0.20	X.X° ±1°
.XXX ±0.10	X.XX° ±0.5°



深圳市华明通电子有限公司
Shenzhen Huamingtong Electronics Co., Ltd

MANUFACTURE DWG

PART NO.	B25410120-APB0513-H25A60
DESIGN:	James
CHED:	Talen
APPD:	Sophia

TITLE: 2.54PH H2.5 1xnPin 180度 PC3.0 PA6.0 PB2.5 L11.5 6T		
CUSTOMER	SIZE	UNITS
	A4	MM
	SCALE	SHEET
	N:A	1/1