


1		2		3		4		5		6		7		8																																																	
A	Dept	晨翔2.54mm排针， 2*38Pin, 直插， 镀金， 黑胶， 胶高2.5mm, 针长11.6mm										REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED																																															
	Qty											A	NEW RELEASE	JLZ 06/22/24'																																																	
	DC	1																																																													
	ED	1																																																													
	IE	1																																																													
B	ISO	1																																																													
	PD	1																																																													
	R&D	1																																																													
	SD	1																																																													
	QA	1																																																													
C	QC	1																																																													
	QE	1																																																													
	晨翔料号： DS1021-2x38SF11-B 															备注：																																															
																1. 电性说明：																																															
																1.1 接触阻抗：20毫欧最大																																															
1.2 耐压：600伏交流电一分钟																																																															
1.3 绝缘阻抗：1000兆欧最小																																																															
D	1.4 额定电流：3安																																																														
	2. 环境特性：																																																														
	2.1 工作温度：-40~+105° C																																																														
	3. 材料：																																																														
	3.1 端子：H62黄铜， 镍底镀金																																																														
E	3.2 胶芯：PBT， 黑色， 阻燃																																																														
	4. 焊接条件：波峰焊250℃， 时间3至5秒																																																														
	5. 产品符合RoHS环保要求																																																														
	PCB板孔参考尺寸																																																														
	公差：±0.05																																																														
F	<table><tr><td colspan="2">GENERAL TOLERANCE</td><td colspan="2">ANGLE TOLERANCE</td><td colspan="2">PROJECTION</td><td colspan="2">TITLE</td></tr><tr><td>X.</td><td>±0.60</td><td>X.</td><td>±5°</td><td colspan="2">mm</td><td colspan="2">PIN HEADER PITCH 2.54mm V/T TYPE</td></tr><tr><td>.X</td><td>±0.38</td><td>X.</td><td>±3°</td><td colspan="2">A4</td><td colspan="2">SERIES DS1021 SERIES</td></tr><tr><td>.XX</td><td>±0.25</td><td>.XX</td><td>±2°</td><td colspan="2"></td><td colspan="2"></td></tr><tr><td colspan="2">DRAWING TYPE</td><td colspan="2">CUSTOMER</td><td colspan="2">SCALE</td><td colspan="2">1:1 SHEET 1 OF 1</td></tr><tr><td colspan="2">DRAWING NO.</td><td colspan="2">C-DS1021-XXXXX-A</td><td colspan="2">DRAWING NO.</td><td colspan="2">C-DS1021-XXXXX-A</td></tr></table>															GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE		X.	±0.60	X.	±5°	mm		PIN HEADER PITCH 2.54mm V/T TYPE		.X	±0.38	X.	±3°	A4		SERIES DS1021 SERIES		.XX	±0.25	.XX	±2°					DRAWING TYPE		CUSTOMER		SCALE		1:1 SHEET 1 OF 1		DRAWING NO.		C-DS1021-XXXXX-A		DRAWING NO.		C-DS1021-XXXXX-A	
	GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE																																																								
	X.	±0.60	X.	±5°	mm		PIN HEADER PITCH 2.54mm V/T TYPE																																																								
	.X	±0.38	X.	±3°	A4		SERIES DS1021 SERIES																																																								
	.XX	±0.25	.XX	±2°																																																											
DRAWING TYPE		CUSTOMER		SCALE		1:1 SHEET 1 OF 1																																																									
DRAWING NO.		C-DS1021-XXXXX-A		DRAWING NO.		C-DS1021-XXXXX-A																																																									
G	晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD																																																														
H																																																															