





Section A-A



Section B-B



Section C-C

Specifications:

规格:

Voltage rating: 150V AC/DC

额定电压: 150V AC/DC

Current rating: 1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage: 500V AC/minute

耐受电压: 500V AC/分钟

Temperature range: -25°C~+85°C

温度范围: -25°C~+85°C

Insulation resistance: 500MΩ min

绝缘电阻: 500MΩ Min

Contact resistance: 30mΩ Max

接触电阻: 30mΩ Max

X9862 T - P V01

① ② ③ ④

1. Series No

2. Category: T-Terminal

3. Material: P-Phosphor Bronze

4. Plating: V01-Gold Flash

SN-Tin Plated

X9862T-PV01	PHOSPHOR BRONZE	AWG#28-32 O.D:0.9mm (Max)	Gold Flash	X9862H
X9862T-PSN			Tin	
PART NO	Material	Wire Range	Plating	Suitable XKB Housing

DSND	SCALE: N/A	MODEL TYPE: 1.25mm Crimp Style Connector
DWN	VIEW:	PART NO.: X9862T-PV01
CHKD	UNIT: mm/in	DWG NO.: X9862T-PV01
APPD	SIZE: A4	WEIGHT
XKB INDUSTRIAL PRECISION CO., LIMITED		SHEET
		REVISION
		1/1
		A0

广东星坤科技股份有限公司

DATE
REVISIONS

文件工程章

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	

XKB