




NOTES:

备注

1.Copper,nickel base,matte tin

黄铜H62, 镍底, 镀雾锡

2.Wire screw hole M4

压线螺孔M4

3.Current Rating: 60A

额定电流: 60A

4.Operating temperature: -40℃ ~ +125℃

工作温度: -40℃ ~ +125℃

5.There shall be no defects such as pin deformation and burrs.

不得有脚变形, 毛刺等缺陷

6.Unmarked dimensions refer to tolerances

未标注的尺寸参考公差



Ordering Information

XD - * * * * - **** - D *** * - 02

Type	Screw Thread	Welding Feet	T=Anti Twist	Series	D=DIP	Product No.	Material
M=Full Teeth (插牙)	3=M3 (螺牙)	101=10x14mm (防止扭动)	0808=8x8mm	101=10x14mm	S=SMT	产品序号	默认=Copper (黄铜)
R=Nut (螺母)	4=M4 (螺牙)	4=4个			FD=Flag Dip		RC=Red Copper (紫铜)
RG=Rivet Gasket (铆垫片)	5=M5 (螺牙)	6=6个					
.....	6=M6 (螺牙)	8=8个					



GENERAL TOLERANCE

制图

02

DIM TOL

审核

X.X ±0.30

批准

X.XX ±0.20

比例

X.XXX ±0.10

SCALE

Angle ±3.0°

投影



深圳讯答科技有限公司

ShenzhenXunDaTechnology Co.,Ltd

产品名称

PCB 焊接端子 (侧插 铆垫片 M4 4焊脚 10x13.5x8mm)

版本

REV.

产品料号

XD-RG44-1013-FD063-02

单位

UNITS

材料

材料

页次

SHEET

1/1