


NOTES:

备注

1.Copper,nickel base,matte tin
黄铜H62, 镍底, 镀雾锡

2.Wire screw hole M6

压线螺孔M6

3.Current Rating: 150A

额定电流: 150A

4. Operating temperature: -40°C ~ +125°C



工作温度: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$

5. There shall be no defects such as pin deformation and burrs.

不得有脚变形，毛刺等缺陷

6. Unmarked dimensions refer to tolerances

未标注的尺寸参考公差




参考安装方式

Ordering Information

XD - * * * * - ***** - D *** * - 02

Type	Screw Thread	Welding Feet	T=Anti Twist (防止扭扭)	Series 0808=8x8mm 1014=10x14mm	D=DIP S=SMD FD=Flag Dip	Product No. 产品序号	Material 材质=Copper (黄铜) R=Nickel Copper (紫铜)
M=Full Teeth (全齿)	3=M3 (螺牙)	1=1x1 (焊脚)					
R=Right Nut (螺帽)	4=M4 (螺牙)	2=2x2 (焊脚)					
	5=M5 (螺牙)	4=4x4 (焊脚)					
R=Right Gasket (螺垫片)	6=M6 (螺牙)	6=6x6 (焊脚)					
	8=M8 (螺牙)	8=8x8 (焊脚)					



GENERAL TOLERANCE		制 图 DRAWING	02	 深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd			
DIM	TOL	审 核 CHECK		产品名称 TITLE	PCB 焊接端子 (侧插 铆垫片 M6 4焊脚 17x20x13mm)	版 本 REV.	A
X.X	±0.30	批 准 APPROVAL		产品料号 PART NO.	XD-RG64-1720-FD018-02	单 位 UNITS	mm
X.XX	±0.20	比 例 SCALE		材 料 MATERIAL		页 次 SHEET	1/1
X.XXX	±0.10	投 影 Projection					
Angle	±0.3°						