






NOTES:

备注


- 1.Copper,nickel base,matte tin
黄铜H62，镍底，镀雾锡
- 2.Wire screw hole M4
压线螺孔M4
- 3.Current Rating: 50A
额定电流：50A
- 4.Operating temperature: -40℃ ~ +125℃
工作温度：-40℃ ~ +125℃
- 5.There shall be no defects such as
pin deformation and burrs.
不得有脚变形，毛刺等缺陷
- 6.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差



Ordering Information

XD - * * * * - ***** - D *** * - 02

Type	Screw Thread	Welding Feet	T=Anti Twist (防止扭动)	Series 0108: 8x8mm 1014: 10x14mm	D=DIP S=SMT F=Flag Dip	Product No. 产品序号	Material 默认=Copper (黄铜) RC=Red Copper (紫铜)
M=Pull Teeth (抽牙)	3=M3 (毫米)						
RN=Rivet Nut (螺母圈)	4=M4 (毫米)	2=2个					
RG=Rivet Gasket (螺母垫片)	5=M5 (毫米)	4=4个					
	6=M6 (毫米)	6=6个					
	8=M8 (毫米)	8=8个					



有限公司					GENERAL TOLERANCE		制图 DRAWING		02		深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd			
					DIM TOL		审 核 CHECK							
					X.X ±0.30		批 准 APPROVAL		产品名称 TITLE		PCB 焊接端子 (插板 铆垫片 M4 4焊脚 7.9x7.9x24.3mm)		版本 REV.	A
			初版发行		X.XX ±0.20 X.XXX ±0.10		比 例 SCALE		产品料号 PART NO.		XD-RG44-0707-D059-02		单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°		投 影 Projection			材料 MATERIAL			页次 SHEET	1/1		