







参考安装方式

NOTES:
备注


- 1.Copper,nickel base,matte tin
黄铜H62, 镍底, 镀雾锡
- 2.Wire screw hole M3
压线螺孔M3
- 3.Current Rating: 50A
额定电流: 50A
- 4.Operating temperature: -40℃ ~ +125℃
工作温度: -40℃ ~ +125℃
- 5.There shall be no defects such as
pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
- 6.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差



Ordering Information

XD - * * * * - * * * - D * * * * - 02

Type	Screw Thread	Welding Feet	T=Anti Twist	Series	Dip	Product No.	Material
M=Full Teeth (插牙)	3=M3 (螺牙)	2=2个 (焊脚)	0808=80mm (防止扭动)	1014=10x14mm	5=5mm Dip	产品序号	默认=Copper (黄铜)
N=Nut (螺母)	4=M4 (螺牙)	2=2个 (焊脚)					RC=Red Copper (紫铜)
G=Gasket (垫片)	5=M5 (螺牙)	4=4个 (焊脚)					
	6=M6 (螺牙)	6=6个 (焊脚)					
	8=M8 (螺牙)	8=8个 (焊脚)					



GENERAL TOLERANCE

制图
DRAWING

02



深圳讯答科技有限公司
ShenzhenXunDaTechnology Co.,Ltd

DIM TOL

审核
CHECK

产品名称
TITLE

PCB 焊接端子 (插板 铆垫片 M3
4焊脚 7.8x7.8x13.5mm)

版本
REV.

A

X.X ±0.30

批准
APPROVAL

产品料号
PART NO.

XD-RG34-0707-D051-02

单位
UNITS

mm

X.XX ±0.20

比例
SCALE


材料
MATERIAL

页次
SHEET

1/1

X.XXX ±0.10

投影
Projection



Angle ±3.0°

序号
No.

变更内容
MODIFY CONTENT

日期
MODIFY DATE

初版发行

24403030674221