





- NOTES:
备注
- 1.Copper,nickel base,matte tin
黄铜H62, 镍底, 镀雾锡
 - 2.Wire screw hole M6
压线螺孔M6
 - 3.Current Rating: 120A
额定电流: 120A
 - 4.Operating temperature: -40℃ ~ +125℃
工作温度: -40℃ ~ +125℃
 - 5.There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
 - 6.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差



Ordering Information

XD - * * * * - **** - D *** * - 02

Type	Screw Thread	Welding Feet	T=Anti Twist	Series	D=DIP	Product No.	Material
M=Full Teeth (插牙) R=Right Nut (螺母) RC=Right Gasket (垫片)	3=M3 (螺牙) 4=M4 (螺牙) 5=M5 (螺牙) 6=M6 (螺牙) 8=M8 (螺牙)	2=2个 4=4个 6=6个 8=8个	0808=8x8mm (防止扭动)	1014=10x14mm	S=SMT FD=Flip Dip	产品序号	默认=Copper (黄铜) RC=Red Copper (紫铜)



GENERAL TOLERANCE		制图 DRAWING	02	深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd		
DIM	TOL	审核 CHECK		产品名称 TITLE	版本 REV.	A
X.X	±0.30	批准 APPROVAL		PCB 焊接端子 (插板 铜垫片 M6 4焊脚 18x14x16mm)		
X.XX	±0.20	比例 SCALE		产品料号 PART NO.	XD-RG64-1814-D064-02	单位 UNITS
X.XXX	±0.10	投影 Projection		材料 MATERIAL		页次 SHEET
Angle	±3.0°					1/1