




- NOTES:
备注
- 1.Copper,nickel base,matte tin
黄铜H62, 镍底, 镀雾锡
 - 2.Wire screw hole M4
压线螺孔M4
 - 3.Current Rating: 60A
额定电流: 60A
 - 4.Operating temperature: -40℃ ~ +125℃
工作温度: -40℃ ~ +125℃
 - 5.There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
 - 6.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差



Ordering Information

XD - * * * * - * * * - D * * * * - 02

Type	Screw Thread	Welding Feet	T=Anti Twist	Series	Dip	Product No.	Material
M=Full Teeth (插牙)	3=M3 (螺牙)	2=2个	(防止扭动)	0608=86mm	S=Snit	产品序号	默认=Copper (黄铜)
RN=Silver Nut (银螺母)	4=M4 (螺牙)	4=4个		1014=10x14mm	F=Flag		RC=Red Copper (紫铜)
RG=Silver Gasket (银垫片)	5=M5 (螺牙)	6=6个			Dip		
	6=M6 (螺牙)	8=8个					



GENERAL TOLERANCE

制图
DRAWING

02



深圳讯答科技有限公司

ShenzhenXunDaTechnology Co.,Ltd

DIM TOL

审核
CHECK

产品名称
TITLE

PCB 焊接端子 (插板 铜垫片 M4
4焊脚 11.1x9.2x10.5mm)

版本
REV.

A

X.X ±0.30

批准
APPROVAL

产品料号
PART NO.

XD-RG44-1109-D055-02

单位
UNITS

mm

X.XX ±0.20

比例
SCALE

材料
MATERIAL

页次
SHEET

1/1

X.XXX ±0.10

投影
Projection

Angle ±3.0°

序号
No.

变更内容
MODIFY CONTENT

日期
MODIFY DATE