








| 修 订 | 标 记  | 修 改 描 要              | 签 名       | 日 期        |
|-----|------|----------------------|-----------|------------|
| REV | MARK | REVISION DESCRIPTION | SIGNATURE | DATE       |
| AO  |      | NEW DRG              |           | 2016-03-12 |



PCB LAYOUT

>4P

2P&3P

| CKT | DimA  | DimB  | DimC  | 序号 | 项目 | 描述  | 备注 |
|-----|-------|-------|-------|----|----|-----|----|
| 2   | 1.25  | 4.40  | 7.40  |    |    |     |    |
| 3   | 2.50  | 5.65  | 8.65  |    |    |     |    |
| 4   | 3.75  | 6.90  | 9.90  |    |    |     |    |
| 5   | 5.00  | 8.15  | 11.15 |    |    |     |    |
| 6   | 6.25  | 9.40  | 12.40 |    |    |     |    |
| 7   | 7.50  | 10.65 | 13.65 |    |    |     |    |
| 8   | 8.75  | 11.90 | 14.90 |    |    |     |    |
| 9   | 10.00 | 13.15 | 16.15 |    |    |     |    |
| 10  | 11.25 | 14.40 | 17.40 |    |    |     |    |
| 11  | 12.50 | 15.65 | 18.65 |    |    |     |    |
| 12  | 13.75 | 16.90 | 19.90 | 1  | 塑胶 | LCP |    |
| 13  | 15.00 | 18.15 | 21.15 | 2  | 端子 | 黄铜  |    |
| 14  | 16.25 | 19.40 | 22.40 | 3  | 焊片 | 黄铜  |    |
| 15  | 17.50 | 20.65 | 23.65 |    |    |     |    |
| 16  | 18.75 | 21.90 | 24.90 |    |    |     |    |



深圳市华德共创科技有限公司  
Shenzhen Huade co-create Technology Co.,LTD  
电话: 0755-23304126 传真: 0755-29940187

| -TOLERANCES-<br>UNLESS OTHERWISE SPECIFIED<br>公差参数表 |            | TITLE:<br>产品名称: MX1.25针座卧贴 |                                   |
|-----------------------------------------------------|------------|----------------------------|-----------------------------------|
| X.X ±0.30                                           | X.X* ±3°   | APPD:<br>核准:               | PART NO:<br>产品编号: HDGC1251WR-S-XP |
| X.XX ±0.20                                          | X.XX* ±2°  | CHECK:<br>校对: 王建业          | DATE SCALE UNIT CODE NUMBER       |
| X.XXX ±0.10                                         | X.XXX* ±1° | DRAW:<br>绘图: 黄艳兰           | 2016-03-12 1:1 mm A001            |