

1

2

3

4

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.07.17	桑 菴

CIRCUIT A

CIRCUIT 1

CIRCUIT B

CIRCUIT C

TYPE A

TYPE B

TYPE C

10.80 [0.426]

(0.80 [0.031])

7.00 [0.276]

8.40 [0.331]

2.50 [0.099]

2.00 [0.079]

规格Specifications:

额定电压Voltage rating:60V AC/DC

额定电流Current rating:3A AC/DC

耐受电压Withstanding voltage:500V AC/minute

温度范围Temperature range:-40℃~+125℃

绝缘电阻Insulation resistance:≥100MΩ

接触电阻Contact resistance:≤10mΩ (测试后≤30mΩ)

PART NO.: X332X H-XX X-PB XX

1.Series No:332A-TYPE A
332B-TYPE B
332C-TYPE C

2.Category:H-Housing

3.Row No.Pin No:XX-See Table A

4.Morphology:Blank-No CPA Feature
C-With CPA Feature

5.Material:PB-PBT

6.Color:Blank-Black; GR-Gray;
BL-Blue

TABLE A

PIN NO.	A	B	C	D
8	10.00		6.00	15.60
12	14.00	15.90	10.00	19.60
16	18.00	19.90	14.00	23.60
20	22.00	23.90	18.00	27.60
24	26.00	27.90	22.00	31.60
28	30.00	31.90	26.00	35.60
32	34.00	35.90	30.00	39.60
40	42.00	43.90	38.00	47.60

X332CH-XXC-PBXX	X332CWRS-XXC	X332XT-BSN	PBT UL94 V-0
X332BH-XXC-PBXX	X332BWRS-XXC	X332XT-BSN	PBT UL94 V-0
X332AH-XXC-PBXX	X332AWRS-XXC	X332XT-BSN	PBT UL94 V-0
X332CH-XX-PBXX	X332CWRS-XX	X332XT-BSN	PBT UL94 V-0
X332BH-XX-PBXX	X332BWRS-XX	X332XT-BSN	PBT UL94 V-0
X332AH-XX-PBXX	X332AWRS-XX	X332XT-BSN	PBT UL94 V-0
PART NO.	Suitable XKB WAFER	Suitable XKB Terminal	MATERIAL

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

DESIGN 桑 菴

CHECKED

APPROVED

VIEW: 

UNIT: mm/in

SIZE: A4

MODEL TYPE:
2.0mm Crimp Style Housing

PART NO.:
X332XH-XXX-PBXX

DWG NO.:

SCALE N/A

PAGE 1/3

REVISION A0

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

XKB INDUSTRIAL PRECISION CO.,LIMITED




1

2


3

4





	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.07.17	桑 葚

NO CPA FEATURE


8 PIN




12 PIN

MATED DIMENSION


16 PIN



20~40 PIN



8~12 PIN



16~40 PIN


ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	桑 菰	VIEW:				MODEL TYPE:	2.0mm Crimp Style Housing		
CHECKED		UNIT: mm/in				PART NO.:	X332XH-XXX-PBXX		
APPROVED		SIZE: A4				DWG NO.:			
PRECISION CO., LIMITED						SCALE	PAGE	REVISION	
						N/A	2/3	A0	

XKB INDUSTRIAL PRECISION CO.,LIMITED

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn



WITH CPA FEATURE

CPA

MATED DIMENSION

(D)

(23.50 [0.925])

(11.05 [0.435])

16~40 PIN

16~40 PIN

ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	桑 菴
CHECKED	
APPROVED	

VIEW:	
UNIT:	mm/in
SIZE:	A4

MODEL TYPE:	2.0mm Crimp Style Housing
PART NO.:	X332XH-XXX-PBXX
DWG NO.:	

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	3/3	A0