








ANGLAR

±5°

X.

±0.40

X.x

±0.30

X.xx

±0.20

X.xxx

±0.15

UNSPECIFIED TOLERANCES

DESIGN

桑 菴

CHECKED

APPROVED

VIEW:

UNIT: mm/in

SIZE: A4

MODEL TYPE:

2.0mm Crimp Style Housing

PART NO.:

X332XH-XXX-PBXX

DWG NO.:

SCALE

N/A

PAGE

3/3

REVISION

A0

www.helloxkb.com

www.helloxkb.cn

www.xk-dg.cn

XKB INDUSTRIAL PRECISION CO.,LIMITED

1

2

3

4

A

B

C

D