



P.C.B. Layout

**Specifications:**

规格:

1. Voltage rating: 125VAC/DC  
额定电压: 125V AC/DC
  2. Current rating: 2A AC/DC  
额定电流: 2A AC/DC
  3. Withstanding voltage: 1000V AC/minute  
耐受电压: ≥1000V AC/分钟
  4. Temperature range: -25°C~+85°C  
温度范围: -25°C~+85°C
  5. Insulation resistance: 1000MΩMIN  
绝缘电阻: ≥1000MΩ
  6. Contact resistance: 20mΩMax  
接触电阻: 20mΩ
  7. Applicable Wire: AWG#22~#30  
适用线规: AWG#22~#30
- Material:**  
材料:
8. Rubber core: PA66 UL94V-2  
胶芯: PA66 UL94V-2
  9. Contact PIN: Brass  
接触针: 黄铜

X2011 W R -XX A - N0 SN  
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category: W-wafer
- ③ Welding Board Angle: R- Straight 90°
- ④ Row No.-Pin No.: XX-2P~16P
- ⑤ Plug the Pin&Special NO:A: With Link Stopper DIP-3.2
- ⑥ Material: N0-Nylon PA66 UL94V-2
- ⑦ Planting Category: SN-Tin Plating

Poles	DIM.A	DIM.B
2P	2.0	6.0
3P	4.0	8.0
4P	6.0	10.0
5P	8.0	12.0
6P	10.0	14.0
7P	12.0	16.0
8P	14.0	18.0
9P	16.0	20.0
10P	18.0	22.0
11P	20.0	24.0
12P	22.0	26.0
13P	24.0	28.0
14P	26.0	30.0
15P	28.0	32.0
16P	30.0	34.0

X2011WR-XXA-N0SN	PA66 UL 94V-2	Brass	Tin-plated	2011H
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: Wire to board connector
DWN		VIEW:	PART NO.: X2011WR-XXA-N0SN
CHKD		UNIT: mm/in	DWG NO.: X-X2011WR-XXA-N0SN
APPD		SIZE: A4	WEIGHT
			SHEET
			REVISION
			1/1
			A0



XKB INDUSTRIAL PRECISION CO., LIMITED

MARK	DESCRIPTION	DATE	REVISED	APPROVED	ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK					L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						