




(2PIN)



(3PIN)



P. C. B Layout

一. 电气性能:

- 1-1. 额定电流: 3A AC DC.
- 1-2. 接触电阻: $\leq 20m\Omega$
- 1-3. 绝缘电阻: $\geq 1000M\Omega$
- 1-4. 耐压: 550V AC/Minute

二. 物理特性:

- 2-1. 操作温度: $-55^{\circ}C \sim 105^{\circ}C$
- 2-2. 焊接温度: $+260^{\circ}C$, 10s max

三. 材质:

- 3-1. 塑胶: PA6T(Black) UL94V-0
- 3-2. 插针: Brass/Gold plated

PIN	A	A1	B	C
4	11.40	10.40	2.00	8.00
6	13.40	12.40	4.00	10.00
8	15.40	14.40	6.00	12.00
10	17.40	16.40	8.00	14.00
12	19.40	18.40	10.00	16.00
14	21.40	20.40	12.00	18.00
16	23.40	22.40	14.00	20.00
18	25.40	24.40	16.00	22.00
20	27.40	26.40	18.00	24.00
22	29.40	28.40	20.00	26.00
24	31.40	30.40	22.00	28.00
26	33.40	32.40	24.00	30.00
28	35.40	34.40	26.00	32.00
30	37.40	36.40	28.00	34.00
32	39.40	38.40	30.00	36.00
34	41.40	40.40	32.00	38.00
36	43.40	42.40	34.00	40.00
38	45.40	44.40	36.00	42.00
40	47.40	46.40	38.00	44.00
42	49.40	48.40	40.00	46.00
44	51.40	50.40	42.00	48.00
46	53.40	52.40	44.00	50.00
48	55.40	54.40	46.00	52.00
50	57.40	56.40	48.00	54.00

浙江博穆精密电子有限公司

图名: 2.0-2xNAT

图号: xxxxxxxxxxxxxxxxxxxxxx

未标注公差

XX.	± 0.40	XX°	$\pm 2^{\circ}$
X.	± 0.30	.XX°	$\pm 1^{\circ}$
.X	± 0.20		
.XX	± 0.15		

绘制:

签发:

审核:

单位: MM

比例: 1:1

视图: