

A

B

C

D

E

F

A

B




C

D

E

F

版本	变更内容	工程确认	日期



Printing date code :

Date
Month
Year
e. g:
11th. Jan. 2022 —220111
The date code can be printed on the front
and opposite sides of the switch

CHARACTERISITICS	
Operating Force:	150gf Max.
Release Force:	30gf Min.
Free Position:	4.90mm Max.
Operation Position:	4.10±0.30mm
Movement-Differential:	0.30mm Max.
Total Travel Position:	2.30mm Max.
PROTECTION GRADE	
SWITCH SEALING:	IP67
ANSCHLUESSE/TERMINALS:	IP00
Ratings	
0.1A 12V DC 50μWA 5V DC 0.1A ~ 1.0A 12VDC	
Circuit Diagram	
COM 1 2 NO	

深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO.,LTD	页码 (SHEET)	1/1	单位(UNIT): MM
	版本 (REV)	A1	比例(SCALE)
	日期 (DATE)	2021. 10. 12	
	设计 (DESIGN)	LUO	DIMENSION ±0.40 ANGLE ±2°
	审核 (CHECKED)	ROGER LI	
品名 (ITEM NO)	8. 3x5. 3 无柱微动开关		
料号 (PART NO)	45YTD-309-13B		
图号 (DWG NO)			
核准 (APPROVED)		ROC ZHAO	

These drawings and specifications are Shenzhen Yiyuan Technology Co Ltd.The property should not be copied. Without Shenzhen Yiyuan Technology Co. Ltd.Prior written consent to copy or use in any way. Email at info@yiyuanswitches.com