







T(terminal)	
A	Solder teminals
B	Straight PCB teminals
C	Others



Circuit Diagram



Printing



CHARACTERISITICS

Operating Force	150gf Max
Release Force	30gf Min
Free Position	4.90mm Max
Operation Position	4.10±0.25mm
Movement-Differential	0.30mm Max
Total Travel Position	2.30mm Max

ELECTRICAL DATA


CONTACT ARRANGEMENT S. P. S. T-NO	SWITCH SEALING IP67
Ratings	
12V DC	0.1 A
5V DC	50 μA

X. ±0.50	X. ° ±2°	UNITS
.X ±0.30	.X° ±1°	mm
.XX ±0.10	.XX° ±0.5°	MAT'L
.XXX ±0.05		FINISH
		Q' TY



深圳市怡远科技有限公司  
SHENZHEN YIYUAN TECHNOLOGY CO.,LTD

PART NO.	45YTD-309-13A
APPD:	ROGER
CHKD:	ROC
DR:	BILLY WANG 2020/08/21

TITLE:			
DETECT SWITCH			
DWG NO. :			
45YTD-309-13A			
	SCALE	SHEET	REV.
	1/1	1/1	A