






PCB. WELDING DRAWING



CIRCUIT DIAGRAM

Specification

Operating Life	300,000
Contact rating	50mA@12V DC.
Insulation resistance	50 Ω min.
Contact resistance	100M Ω max. initial.
Dielectric Strength	250 V AC(1mm)
Travel	0.35±0.2mm
Storage Temperature	- 30° C to 80° C

Mechanical

E	Button	Silica	1	Pickling
D	COVER	Stainless Steel	1	Cleaning
C	DOME	Stainless Steel	1	Plated Ag
B	HOUSING	PPA	1	Black
A	PIN	PHOSPHOR BRONZE	1	Plated Ag
ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR

Type	Operatin g Force (gf)	Height mm	Button	Leads Shape (G, J, T)	Ground pin (0, 1)	Pegs Option (0, 1)
YTS2K008	4	400gf±50	H	5.5	E (Ecru) U (Bale) W (White)	J
			G	5.2		
	3	250gf±50	F	4.8		
			E	4.5		
	2	160gf±50	D	4.3		
			C	3.8		
	1	100gf±50	B	3.5		
			A	3.1		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD
Email at info@yiyuanswitches.com

UNITS
mm

MAT'L

FINISH

Q'TY



深圳市怡远科技有限公司
SHENZHEN YIYUAN TECHNOLOGY CO.,LTD

PART NO.
YTS2K008

TITLE:
TACTILE SWITCH 6.2*6.2 触敏开关


APPD: ROGER

DWG NO.:

YTS2K008

CHKD: RDC

DR: BILLY WANG 2020/08/21



SCALE	SHEET	REV.
1/1	1/1	A1

Packaging:

Reel of 1,500 pieces for 3.1-3.5H

Reel of 1,000 pieces for 4.3~5.5H