

8		7		6		5		4		3		2		1											
RoHS								REV	ECN NO.		DESRIPTION		DESIGN		APPROVAL		DATE								
								A1	NEW		更换图框						2024.05.24								
P1 100±3 3.0±0.5脱皮浸锡 ① 3.0±0.5脱皮浸锡 P2																									
技术要求： 1.1.端子铆接牢固，无松动，脱落等现象； 1.2.线材印字清晰，无破损划伤； 2.外观要求按品质管理部检验标准执行 3.包装要求按包装作业指引或客户指定包装要求																									
				X.±0.50 X.°± .X±0.25 .X°± .XX±0.15 .XX°± .XXX±0.10 .XXX°± UNITS: mm		PART NO: XF7124 TITLE: UL1007/24 黄色 L=100 双端上锡3.0MM				XFCN兴飞连接器 0769-82001899 www.xfconn.com DWG NO: /															
① 序号 NO.				线材 部件 PARTS		UL1007 24#黄色 线材 端子（部件） 胶壳 Cable, Terminal (Part) Housing				1PCS 数量 Quantity		THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN				APPD CHKD DRAW DATE		Chen ZhiQiang Liu Wei Chen HongJiang 2024.11.02		VIEW SCALE NONE		⊕ SHEET 1/1		REV A1	
物料明细表 Material list																									
8		7		6		5		4		3		2		1											