




CIRCUIT DIAGRAM



PCB. WELDING DRAWING

Specification

Operating Life	100,000
Contact rating	50mA@12V DC.
Insulation resistance	100MΩ min.
Contact resistance	100mΩ max.initial.
Dielectric Strength	250 V AC(1mn)
Travel	0.35±0.15mm
Storage Temperature	- 30° C to 85° C

Mechanical

E	STEM	PPA	1	Yellow/Black	PN	Operating Force (gf)	Height mm	Stem (Yellow/Black)	Pegs Option
D	COVER	Stainless Steel	1	Clean	YTS2B0031ABT00	160±50	7.3	Black	0 (None)
C	DOME	Stainless Steel	1	Plated Ag	YTS2B0032ABT00	250±50	7.3	Black	0 (None)
B	HOUSING	PPA	1	White	YTS2B0031AYT00	160±50	7.3	Black	1 (Pegs)
A	PIN	Brass	1	Plated Ag	YTS2B0032AYT00	250±50	7.3	Black	1 (Pegs)
ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR	YTS2B0031AYT01	160±50	7.3	Yellow	0 (None)
					YTS2B0032AYT01	250±50	7.3	Yellow	1 (Pegs)

X. ±0.50	X.° ±2°	UNITS
.X ±0.30	.X° ±1°	mm
.XX ±0.10	.XX° ±0.5°	MAT'L
.XXX ±0.05		
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD Email at info@yiyuanswitches.com		FINISH
		Q' TY



深圳市怡远科技有限公司
SHENZHEN YIYUAN TECHNOLOGY CO.,LTD

PART NO. YTS2B003	TITLE: TACTILE SWITCH 12x12
APPD: ROGER	DWG NO. : YTS2B003
CHKD: ROC	SCALE SHEET REV.
DR: BILLY WANG 2020/08/21	1/1 1/1 A1

Packaging:
Reel of 1,000 pieces.