







| Part No      | Pin | A    | B     | Part No      | Pin | A     | B     |
|--------------|-----|------|-------|--------------|-----|-------|-------|
| ZX-0.8-2PLT  | 2   | 0.80 | 3.85  | ZX-0.8-14PLT | 14  | 10.40 | 13.45 |
| ZX-0.8-3PLT  | 3   | 1.60 | 4.65  | ZX-0.8-15PLT | 15  | 11.20 | 14.25 |
| ZX-0.8-4PLT  | 4   | 2.40 | 5.45  | ZX-0.8-16PLT | 16  | 12.00 | 15.05 |
| ZX-0.8-5PLT  | 5   | 3.20 | 6.25  | ZX-0.8-17PLT | 17  | 12.80 | 15.85 |
| ZX-0.8-6PLT  | 6   | 4.00 | 7.05  | ZX-0.8-18PLT | 18  | 13.60 | 16.65 |
| ZX-0.8-7PLT  | 7   | 4.80 | 7.85  | ZX-0.8-19PLT | 19  | 14.40 | 17.45 |
| ZX-0.8-8PLT  | 8   | 5.60 | 8.65  | ZX-0.8-20PLT | 20  | 15.20 | 18.25 |
| ZX-0.8-9PLT  | 9   | 6.40 | 9.45  | ZX-0.8-21PLT | 21  | 16.00 | 19.05 |
| ZX-0.8-10PLT | 10  | 7.20 | 10.25 | ZX-0.8-22PLT | 22  | 16.80 | 19.85 |
| ZX-0.8-11PLT | 11  | 8.00 | 11.05 | ZX-0.8-23PLT | 23  | 17.60 | 20.65 |
| ZX-0.8-12PLT | 12  | 8.80 | 11.85 | ZX-0.8-24PLT | 24  | 18.40 | 21.45 |
| ZX-0.8-13PLT | 13  | 9.60 | 12.65 |              |     |       |       |

#### NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

#### SPECIFICATIONS:

- 1.Spacing: 0.8
- 2.Voltage Rating: 30V AC DC
- 3.Current Rating: 0.5A AC DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 200V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

|                   |            |                |       |             |     |                  |              |                                                                                       |   |
|-------------------|------------|----------------|-------|-------------|-----|------------------|--------------|---------------------------------------------------------------------------------------|---|
| GENEERL TOLERANCE |            | 制图<br>DRAWING  | Yu    |             |     | 料号<br>PART NO.   | ZX-0.8-nPLT  | 版本<br>REV.                                                                            | A |
| X.±0.25           | X.*±2°     |                |       |             |     | 品名<br>TITLE      | WAFER 0.8 立贴 | 页次<br>SHEET                                                                           |   |
| .X±0.20           | .X*±1°     | 审核<br>CHECK    | HUANG |             |     | 客户料号<br>CUTM.NO. |              |  |   |
| .XX±0.15          | .XX*±0.5°  | 核准<br>APPROVAL |       |             |     | RUAN             |              |                                                                                       |   |
| .XXX±0.10         | .XXX*±0.5° | 单位<br>UNITS    | MM    | 比例<br>SCALE | 1:1 |                  |              |                                                                                       |   |