








RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.

REV.	ECN. NO.	APPD.



电路图




PCB. 焊接图

		F	Hat	PPA	1	Temperature resistance 280°C
Operating Life	100,000	E	Pin	Orichalcum	1	Silver plating
Contact rating	50mA@12V DC.	D	Mount	PPA	1	Temperature resistance 280°C (Black)
Insulation resistance	100MΩ min.	C	Reed	Stainless steel	1	Plated Ag
Contact resistance	50mΩ max.initial.	B	Cover	Orichalcum	1	Tinning
Dielectric Strength	250 V AC(1mm)	A	Button	PPA	1	Temperature resistance 280°C
Travel	0.35±0.1mm	ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR

Mechanical

Type	Operating Force (gf)	Height mm	Button	Leads Shape (G, J, T)	Ground pin (0, 1)	Pegs Option (0, 1)
YTS2B005	1:180±50G F 2: 260±50 GF	A 7.3	B (Black)	G	0 (None)	0 (None)

≥0~2< ≥2~5< ≥5 角度 ANGLE		±0.15 ±0.25 ±0.35 ±0.5°	UNITS mm	YUAN 深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO.,LTD							
MAT'L 			Series NO. YTS2B005	TITLE: TACTILE SWITCH							
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD Email at info@yiyuanswitches.com			FINISH 	APPD: ROGER	DWG NO.: YTS2B005						
			Q'TY 	CHKD: ROC							
			DR: BILLY WANG 2020/08/21		<table><tr><td>SCALE</td><td>SHEET</td><td>REV.</td></tr><tr><td>1/1</td><td>1/1</td><td>A1</td></tr></table>	SCALE	SHEET	REV.	1/1	1/1	A1
SCALE	SHEET	REV.									
1/1	1/1	A1									