







RoHS



T(terminal)	
A	Solder teminals
B	Straight PCB teminals
C	Others

Circuit Diagram



Printing :

Date
Month
Year

CHARACTERISITICS		ELECTRICAL DATA	
Operating Force:	150gf Max.	CONTACT ARRANGEMENT	SWITCH SEALING
Release Force:	30gf Min.	S. P. S. T-NO	IP67
Free Position:	7.90mm Max.	Ratings	
Operation Position:	7.10±0.25mm		
Movement-Differential:	0.30mm Max.		
Total Travel Position:	5.30mm Max.		
		12V DC	0.1A
		5V DC	50 μA



深圳市怡远科技有限公司
SHENZHEN YIYUAN TECHNOLOGY CO.,LTD

品名 (ITEM NO)	8.3x5.3 单柱 接线
料号 (PART NO)	45YTD-309-12A
图号 (DWG NO)	

页码 (SHEET)	1/1	单位(UNIT) : MM
版本 (REV)	A1	比例(SCALE)
日期 (DATE)	2021. 10. 12	DIMENSION ±0.40 ANGLE ±2°
设计 (DESIGN)	LUO	
审核 (CHECKED)	ROGER LI	
核准 (APPROVED)	ROC ZHAO	

These drawings and specifications are Shenzhen Yiyuan Technology Co Ltd.The property should not be copied. Without Shenzhen Yiyuan Technology Co. Ltd.Prior written consent to copy or use in any way. Email at info@yiyuanswitches.com