

P/N	PIN	DIM.A	DIM.B
IDC2.54-05-03PWS	2*3	5.08	7.62
IDC2.54-05-04PWS	2*4	7.62	10.16
IDC2.54-05-05PWS	2*5	10.16	12.70
IDC2.54-05-06PWS	2*6	12.70	15.24
IDC2.54-05-07PWS	2*7	15.24	17.78
IDC2.54-05-08PWS	2*8	17.78	20.32
IDC2.54-05-09PWS	2*9	20.32	22.86
IDC2.54-05-10PWS	2*10	22.86	25.40
IDC2.54-05-12PWS	2*12	27.94	30.48
IDC2.54-05-13PWS	2*13	30.48	33.02
IDC2.54-05-14PWS	2*14	33.02	35.56
IDC2.54-05-15PWS	2*15	35.56	38.10
IDC2.54-05-16PWS	2*16	38.10	40.64
IDC2.54-05-17PWS	2*17	40.64	43.18
IDC2.54-05-18PWS	2*18	43.18	45.72
IDC2.54-05-20PWS	2*20	48.26	50.80
IDC2.54-05-22PWS	2*22	53.34	55.88
IDC2.54-05-25PWS	2*25	60.96	63.50
IDC2.54-05-30PWS	2*30	73.66	76.20
IDC2.54-05-32PWS	2*32	78.74	81.28

SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Insulator Material: Polyester(UL 94V-0)
Contact plating: Gold Flash
Standard: PA6T
Max.Processing Temp: 240°C for30-60seconds
(260°Cfor10seconds)

PART NUMBER DESCRIPTION:




IDC2.54-05-NPWS

(D=单排;S=双排)

(Z=直脚;W=弯脚)

(PIN数量;06.....64PIN)

(排针开关)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:2.0DC3-nPin H5.7 90度 PC2.8 PB9.3 L10.5/14.5 6T
DECIMALS:	ANGLES:		PAR IDC2.54-05-NPWS
X.±0.30	X°±5'		DWN
X.X±0.20	X.X°±1'		CHKD
X.XX±0.10	X.XX°±0.5'	CUSTOMER COPY	
		SCALE N:A	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A