







SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)



PCB TOLERANCE:±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
FH2.54-09-01PZS	2*1	0.00	2.54
FH2.54-09-02PZS	2*2	2.54	5.08
FH2.54-09-03PZS	2*3	5.08	7.62
FH2.54-09-04PZS	2*4	7.62	10.16
FH2.54-09-05PZS	2*5	10.16	12.70
FH2.54-09-06PZS	2*6	12.70	15.24
FH2.54-09-07PZS	2*7	15.24	17.78
FH2.54-09-08PZS	2*8	17.78	20.32
FH2.54-09-09PZS	2*9	20.32	22.86
.....			
FH2.54-09-40PZS	2*40	(PIN-1)X2.54	(PIN)X2.54

PART NUMBER DESCRIPTION:

FH2.54-09-NPZS

(D=单排;S=双排)

(Z=直脚;W=弯脚)

(PIN数量;01.....40PIN)

(排针开关)

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:2.54FH H8.5 2xnPin 180度 Y型 PC3.2 6T
			PAR FH2.54-09-NPZS
DECIMALS:	ANGLES:		DWN
X.±0.30	X°±5'		CHKD
X.X±0.20	X.X°±1'	CUSTOMER COPY	APVD
X.XX±0.10	X.XX°±0.5'		SCALE N:A
		SIZE:A4	UNIT:MM
		SHEET:1F1	REV:A